



2 Type

- A without dowel hole
- B with dowel hole



d₁ Thread	d₂ H7 Bore	d₃	d₄	d₅ H11	e	h	k	l
M 5	B 5	14	20	1,5	2,5	12	8	7
M 6	B 6	16	24	1,5	2,5	14	10	8
M 8	B 8	20	30	2	3	17	12	10
M 10	B 10	28	36	3	4	20	14	12
M 12	B 12	32	40	4	4	24	16	16

Specification

- Steel
- Tensile strength class 5 (500 N/mm²)
- blackened
- *ISO-Fundamental Tolerances* → Page 1132
- **RoHS compliant**

Information

The dowel bore d_5 in the DIN 6303 knurled nut is designed for the use of clamping or notch pins.

DIN 6303 knurled nuts with H7 bore and the size M12 are not provided for on the official standard sheet.

see also...

- *Quick release-Knurled nuts GN 6303.1* → Page 324

How to order

DIN 6303-M8-A

1 d_1 (d_2)

2 Type