


# ROTEX® Flexible jaw couplings

## Properties of standard spiders


ROTEX® 14




ROTEX® 19




ROTEX® 24 - 65



ROTEX® 75 - 160







ROTEX® 180




### Degree of hardness



Spider type (Shore hardness)	92 Shore A (T-PUR®)	92 Shore A
	 T-PUR®	
Size	14 to 180	14 to 90
Material	T-PUR®	Polyurethane (PUR)
Permissible temperature range		
Permanent temperature	-50 °C to +120 °C	-40 °C to +90 °C
Short-term temperature	-50 °C to +150 °C	-50 °C to +120 °C
Features	<ul style="list-style-type: none"> <li>- significantly higher service life expectancy</li> <li>- very good temperature resistance</li> <li>- improved damping of vibrations</li> <li>- good damping, average flexibility</li> <li>- suitable for all hub materials</li> </ul>	<ul style="list-style-type: none"> <li>- good damping, average flexibility</li> <li>- suitable for all hub materials</li> </ul>

Spider type (Shore hardness)	98 Shore A (T-PUR®) <sup>1)</sup>	98 Shore A <sup>1)</sup>
	 T-PUR®	
Size	14 to 180	14 to 90
Material	T-PUR®	Polyurethane (PUR)
Permissible temperature range		
Permanent temperature	-50 °C to +120 °C	-30 °C to +90 °C
Short-term temperature	-50 °C to +150 °C	-40 °C to +120 °C
Features	<ul style="list-style-type: none"> <li>- significantly higher service life expectancy</li> <li>- very good temperature resistance</li> <li>- improved damping of vibrations</li> <li>- transmission of high torques with average damping</li> <li>- recommended hub material: steel, GJL and GJS</li> </ul>	<ul style="list-style-type: none"> <li>- transmission of high torques with average damping</li> <li>- recommended hub material: steel, GJL and GJS</li> </ul>

Spider type (Shore hardness)	64 Shore D (T-PUR®)
	 T-PUR®
Size	14 to 180
Material	T-PUR®
Permissible temperature range	
Permanent temperature	-50 °C to +120 °C
Short-term temperature	-50 °C to +150 °C
Features	<ul style="list-style-type: none"> <li>- significantly higher service life expectancy</li> <li>- very good temperature resistance</li> <li>- improved damping of vibrations</li> <li>- transmission of very high torques with low damping</li> <li>- recommended hub material: steel and GJS</li> </ul>